



MALE

FEMALE

P1	P2
1	1
26	26
2	2
27	27
3	3
28	28
4	4
29	29
5	5
30	30
6	6
31	31
7	7
32	32
8	8
33	33

P1	P2
9	9
34	34
10	10
35	35
11	11
36	36
12	12
37	37
13	13
38	38
14	14
39	39
15	15
40	40
16	16
41	41

P1	P2
17	17
42	42
18	18
43	43
19	19
44	44
20	20
45	45
21	21
46	46
22	22
47	47
23	23
48	48
24	24
49	49
25	25
50	50

P/N	L	A
25-3-PC-5-GY	1524	50.8
25-3-PC-10-GY	3048	50.8
25-3-PC-15-GY	4572	102
25-3-PC-20-GY	6096	102
25-3-PC-25-GY	7620	102
25-3-PC-30-GY	9144	102
25-3-PC-40-GY	12192	1.5% L
25-3-PC-50-GY	15240	
25-3-PC-75-GY	22860	
25-3-PC-100-GY	30480	
25-3-PC-150-GY	45720	
25-3-PC-200-GY	60950	

QTY	DESCRIPTION
11	1 CONN: 50P F GRAY
10	50 TERMINAL: F G/F P/N: A023-1
9	1 DUSTPROOF COVER: BLUE
8	1 DUSTPROOF COVER: RED
7	A/R PVC TUBE
6	2 CABLE CLIP: 50P GRAY
5	2 PLASTIC SHELL: 50P GRAY
4	50 TERMINAL: M G/F P/N : A020-1
3	2 SCREW: #4-40 * L13.8mm
2	1 CONN: 50P M GRAY
7	A/R CABLE: 24AWG * 25P GRAY

**NOTES:**

- 100% PASS CONTINUITY TEST
- CAT3 RATED
- UL LISTING: E154502



**Allen Tel Products, Inc.**  
30 TV5 DRIVE • HENDERSON, NV • 89014



**25-3-PC-XX-GY**  
**MALE-FEMALE CONNECTORIZED CABLES**