



## TRACJACK MODULE F CONNECTOR F/F, ELECTRICAL IVORY

OR-63700006-13 | [Ortronics](#)

### FEATURES & BENEFITS

TracJack Module provides a single F-connector coupler F/F with under .2dB of insertion loss at 2GHz (1/3 the loss of standard models). TracJack is a versatile single jack solution in a front-load footprint which allows a choice of up to six jacks/connectors to fit in a single gang plate



- F Connector coupler F/F
- Front removable
- Standard TracJack footprint

### SPECIFICATIONS

#### GENERAL INFO

Color: Electrical Ivory  
Footprint: TracJack  
Number Of Ports: 2  
Product Series: TracJack  
Type: Video

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CUL Listing No: E131600  
UL Listing No: E131600

#### CONSTRUCTION INFORMATION

Component 1: Plastic Series II Housing  
Component 2: F-Connector female/female coupler  
Material 1: High Impact Thermoplastic ABS 94V-0

Material 2: Feed-through, RG6/59 (G-F81TN)

#### **DIMENSIONS**

Depth (Metric): 14.48 mm

Height (Metric): 23.37 mm

Height (US): 0.92"

Width (Metric): 18.54 mm

#### **TECHNICAL INFORMATION**

Equipment Type: F Conn Coax

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MALAYSIA

Buy American Act Status: Exception

Note: Contact Customer Support for Buy American Act options