



Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control circuit	Separate control circuit

Complementary

[Uc] control circuit voltage	220 V AC 50 Hz 240 V AC 60 Hz
[In] rated current	20 A tungsten 30 A fluorescent
Poles description	12P 12 NO
Control type	No control units
Local signalling	No indicator
Electrical connection	Screw-clamp terminals

Environment

NEMA degree of protection	Not rated (open device)
product certifications	CSA UL listed

Offer Sustainability

Not Green Premium product	Not Green Premium product
Compliant - since 1431 - Schneider Electric declaration of conformity	Compliant - since 1431 - Schneider Electric declaration of conformity
Available	Available
Need no specific recycling operations	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.