



ATP2000W

Adaptive Technology, Passive Infrared

- “Install and forget” operation
- Passive infrared technology
- Dual 120/277V AC operation, no neutral required
- 1200 sq. ft. coverage
- Built-in photocell for daylight harvesting
- Wallplate included
- Steel mounting strap
- Compatible with most LED and CFL
- CEC Title 24 Compliant
- cULus

Description	Color	Standard	with Nightlight	with Neutral	with Nightlight and Neutral
Adaptive auto-adjusting; selectable manual/auto-ON operation; dual-voltage 120/277V AC; 3-way capable	Gray	ATP2000GY	ATP2000NGY	—	—
	Ivory	ATP2000I	ATP2000NI	ATP2004I	ATP2004NI
	Light Almond	ATP2000LA	ATP2000NLA	—	—
	White	ATP2000W	ATP2000NW	ATP2004W	ATP2004NW

Note: See page E-17 for technical specifications, coverage patterns and wiring schematics.



WS2000W
WS1000W

Passive Infrared

- Passive infrared technology
- Manual adjustment time delay (20 sec. to 30 min.)
- Photocell (WS2000 series)
- No neutral required
- 1200 sq. ft. coverage
- Wallplate included
- Steel mounting strap
- Compatible with most LED and CFL
- CEC Title 24 Compliant
- cULus

Description	Color	Standard	with Nightlight	with Neutral	with Nightlight and Neutral
Manual adjusting; selectable manual/auto-ON operation; dual-voltage 120/277V AC; 3-way capable	Gray	WS2000GY	WS2000NGY	—	—
	Ivory	WS2000I	WS2000NI	WS2004I	WS2004NI
	Light Almond	WS2000LA	WS2000NLA	—	—
	White	WS2000W	WS2000NW	WS2004W	WS2004NW
Manual adjusting; auto-ON operation; 120V AC only	Ivory	WS1000I	WS1000NI	—	—
	White	WS1000W	WS1000NW	—	—
Manual adjusting; Manual-ON operation; 120V AC only	Ivory	WS1001I	WS1001NI	—	—
	White	WS1001W	WS1001NW	—	—

Note: See page E-17 for technical specifications, coverage patterns and wiring schematics.



DT2000W

Digital Timer

Description	Color	Catalog Number
Dip switch enabled preset intervals, user adjustable up to 4 hours, 3-way capable, 960W @ 120V AC and 1200W @ 277V AC. Includes an ON/OFF momentary push button switch feature.	White	DT2000W



DT5030W

Count Down Timers

Description	Color	30 Minutes: OFF, 5, 10, 20, 30	60 Minutes: OFF, 15, 30, 45, 60	12 Hours: OFF, 2, 4, 8, 12
1000W @ 120V AC and 1400W @ 277V AC	Ivory	DT5030I	DT5060I	DT5012I
	Light Almond	DT5030LA	DT5060LA	DT5012LA
	White	DT5030W	DT5060W	DT5012W

Low Voltage Switches

- Attractive, architectural design
- Available latching or momentary contact
- Mounts to standard single gang box
- 2-year warranty

Description	Color	Catalog Number
Low voltage switch, latching, 1 button	Ivory	DSL30I1
	White	DSL30W1
Low voltage switch, momentary, 1 button	Ivory	DSM30I1
	White	DSM30W1
Low voltage switch, momentary, 2 button	Ivory	DSM30I2
	White	DSM30W2

Note: Wallplate sold separately.



DSL30W1
DSM30W1