



**ATP2000W**

**Adaptive Technology, Passive Infrared**

- “Install and forget” operation
- Passive infrared technology
- Dual 120/277V AC operation, no neutral required
- 1200 sq. ft. coverage
- Built-in photocell for daylight harvesting
- Wallplate included
- Steel mounting strap
- Compatible with most LED and CFL
- CEC Title 24 Compliant
- cULus

Description	Color	Standard	with Nightlight	with Neutral	with Nightlight and Neutral
Adaptive auto-adjusting; selectable manual/auto-ON operation; dual-voltage 120/277V AC; 3-way capable	Gray	<b>ATP2000GY</b>	<b>ATP2000NGY</b>	—	—
	Ivory	<b>ATP2000I</b>	<b>ATP2000NI</b>	<b>ATP2004I</b>	<b>ATP2004NI</b>
	Light Almond	<b>ATP2000LA</b>	<b>ATP2000NLA</b>	—	—
	White	<b>ATP2000W</b>	<b>ATP2000NW</b>	<b>ATP2004W</b>	<b>ATP2004NW</b>

Note: See page E-17 for technical specifications, coverage patterns and wiring schematics.



**WS2000W**  
**WS1000W**

**Passive Infrared**

- Passive infrared technology
- Manual adjustment time delay (20 sec. to 30 min.)
- Photocell (WS2000 series)
- No neutral required
- 1200 sq. ft. coverage
- Wallplate included
- Steel mounting strap
- Compatible with most LED and CFL
- CEC Title 24 Compliant
- cULus

Description	Color	Standard	with Nightlight	with Neutral	with Nightlight and Neutral
Manual adjusting; selectable manual/auto-ON operation; dual-voltage 120/277V AC; 3-way capable	Gray	<b>WS2000GY</b>	<b>WS2000NGY</b>	—	—
	Ivory	<b>WS2000I</b>	<b>WS2000NI</b>	<b>WS2004I</b>	<b>WS2004NI</b>
	Light Almond	<b>WS2000LA</b>	<b>WS2000NLA</b>	—	—
	White	<b>WS2000W</b>	<b>WS2000NW</b>	<b>WS2004W</b>	<b>WS2004NW</b>
Manual adjusting; auto-ON operation; 120V AC only	Ivory	<b>WS1000I</b>	<b>WS1000NI</b>	—	—
	White	<b>WS1000W</b>	<b>WS1000NW</b>	—	—
Manual adjusting; Manual-ON operation; 120V AC only	Ivory	<b>WS1001I</b>	<b>WS1001NI</b>	—	—
	White	<b>WS1001W</b>	<b>WS1001NW</b>	—	—

Note: See page E-17 for technical specifications, coverage patterns and wiring schematics.



**DT2000W**

**Digital Timer**

Description	Color	Catalog Number
Dip switch enabled preset intervals, user adjustable up to 4 hours, 3-way capable, 960W @ 120V AC and 1200W @ 277V AC. Includes an ON/OFF momentary push button switch feature.	White	<b>DT2000W</b>



**DT5030W**

**Count Down Timers**

Description	Color	30 Minutes: OFF, 5, 10, 20, 30	60 Minutes: OFF, 15, 30, 45, 60	12 Hours: OFF, 2, 4, 8, 12
1000W @ 120V AC and 1400W @ 277V AC	Ivory	<b>DT5030I</b>	<b>DT5060I</b>	<b>DT5012I</b>
	Light Almond	<b>DT5030LA</b>	<b>DT5060LA</b>	<b>DT5012LA</b>
	White	<b>DT5030W</b>	<b>DT5060W</b>	<b>DT5012W</b>

**Low Voltage Switches**

- Attractive, architectural design
- Available latching or momentary contact
- Mounts to standard single gang box
- 2-year warranty

Description	Color	Catalog Number
Low voltage switch, latching, 1 button	Ivory	<b>DSL30I1</b>
	White	<b>DSL30W1</b>
Low voltage switch, momentary, 1 button	Ivory	<b>DSM30I1</b>
	White	<b>DSM30W1</b>
Low voltage switch, momentary, 2 button	Ivory	<b>DSM30I2</b>
	White	<b>DSM30W2</b>

Note: Wallplate sold separately.



**DSL30W1**  
**DSM30W1**