



Energy Saver T2

EL/mdTQS 18W T2

The Philips EnergySaver T2 provides energy efficient lighting in a smaller, sleeker, size that fits more fixtures. The energy saving T2 is a direct replacement for most incandescents, provides soft white light and lasts 11 years* reducing the hassle of frequent replacements.


Product data

General Information		Lamp Current (Nom)	
Cap-Base	E26 [Single Contact Medium Screw]	Wattage Equivalent	75 W
Nominal Lifetime (Nom)	10000 h	Warm Up Time To 60% Light (Min)	5 s
Switching Cycle	5000X	Warm Up Time To 60% Light (Max)	40 s
		Power Factor (Nom)	0.55
		Voltage (Nom)	110-127 V
Light Technical		Controls and Dimming	
Color Code	827 [CCT of 2700K]	Dimmable	No
Initial lumen (Nom)	1250 lm		
Luminous Flux (Rated) (Nom)	1250 lm	Approval and Application	
Color Designation	Warm White (WW)	Energy Efficiency Label (EEL)	A
Lumen Maintenance 2000 h (Nom)	85 %	Mercury (Hg) Content (Max)	2 mg
Lumen Maintenance 5000 h (Nom)	70 %	Energy Consumption kWh/1000 h	18 kWh
Chromaticity Coordinate X (Nom)	459		
Chromaticity Coordinate Y (Nom)	412	Product Data	
Correlated Color Temperature (Nom)	2700 K	Order product name	EL/mdTQ 18W T2
Luminous Efficacy (rated) (Nom)	67 lm/W	EAN/UPC - Product	046677414009
Color Rendering Index (Nom)	81	Order code	414003
LLMF At End Of Nominal Lifetime (Nom)	50 %	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	6
Operating and Electrical		Material Nr. (12NC)	929689749701
Input Frequency	50 or 60 Hz		
Power (Rated) (Nom)	18.0 W		

Energy Saver T2

Net Weight (Piece)	0.072 kg
--------------------	----------

Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/mdTQ 18W T2	56.5 mm	114.3 mm	47 mm

TORNADO T2 18W/827 E26 110-127V 50/60Hz

