



Main

Product or component type	Miniature circuit-breaker
Range of product	Homeline
Line Rated Current	20 A
Product certifications	UL listed
System Voltage	120 V AC
Mounting mode	Plug-in
Poles description	1P
Short-circuit current	10 kA
Number of spaces required	1
Circuit breaker type	Standard
Circuit breaker application	HACR and Switching Duty rated
Electrical connection	Clamp terminal for 2 cables
AWG gauge	AWG 14...AWG 8 for 1 cable(s) (aluminium/copper) AWG 14...AWG 10 for 2 cable(s) (copper)
Height	3.13 in
Width	1 in
Depth	2.98 in

Complementary

Environment

ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

Offer Sustainability

Green Premium product	Green Premium product
Compliant - since 0701 - Schneider Electric declaration of conformity	Compliant - since 0701 - Schneider Electric declaration of conformity
Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold
Available	Available
Need no specific recycling operations	Need no specific recycling operations

Contractual warranty

Warranty period	Lifetime
-----------------	----------