



## Main

Product or component type	Load Center
Range of product	Homeline
Load center type	Main lugs
Line Rated Current	125 A
Number of spaces	4
Number of circuits	8
NEMA degree of protection	NEMA 3R outdoor
Cover type	Surface cover
Electrical connection	Lugs
Provided equipment	Grounding bar (1)

## Complementary

Short-circuit current	10 kA
Number of tandem circuit breakers	4
Phase	1 phase
System Voltage	120/240 V AC
AWG gauge	AWG 14...AWG 2/0 (copper) AWG 12...AWG 2/0 (aluminium)
Wiring configuration	3-wire
Cover finish	Gray baked enamel
Material	Tin plated aluminium busbar
Enclosure material	Welded galvanized steel
Surface finish	Baked enamel grey
Box number	15R
Height	376 mm
Width	8.9 in (226 mm)
Depth	4.25 in (108 mm)

## Environment

product certifications	UL E-6294
------------------------	-----------

## Offer Sustainability

Green Premium product	Green Premium product
Compliant - since 1248 - Schneider Electric declaration of conformity	Compliant - since 1248 - Schneider Electric declaration of conformity
Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold
Available	Available
Need no specific recycling operations	Need no specific recycling operations
WARNING: This product can expose you to chemicals including:	WARNING: This product can expose you to chemicals including:
Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	Lifetime
-----------------	----------

