

TELEDEX®

SMALL FOOTPRINT.
ELEGANT LINES.



I SERIES

(formerly Teledex iPhone™)

Accept no substitutes.



I Series VoIP

- Single or Two line speakerphones
- VoIP-based protocol; SIP RFC 3261 compliant
- Codecs supported: G711a; G711µ; G729
- Corded Supports 802.1Q VLAN tagging
- 2-port 10/100 ethernet switch
- Supports 802.1Q VLAN tagging
- Supports DHCP or static IP address
- Electronic 3-way conference*; Hold, Mute, Redial keys
- Cordless: Supports up to five handsets, including one on the base and four remotes (RediDock kits); AutoSync – handset automatically syncs with base unit when in cradle
- 5 or 10 Configurable Guest Service Keys
- ADA-compliant volume control with enhanced Sonica™ hearing aid compatibility
- Corded: Visual message waiting indicator
- Cordless: Bright message waiting indicator and positive charge indicator
- Cordless: Optional remote cordless handset battery backup

*Two-line only

I Series Cordless Series Analog

- Single or Two line speakerphones
- OneTouch voice mail access
- Electronic 3-way conference*
- Cordless: PrimeLine/RingLine™ automatic line selection*
- 5 or 10 Configurable Guest Service Keys
- ADA-compliant volume control with enhanced Sonica™ hearing aid compatibility
- Corded: Flash, Hold, Mute, Conference*, Redial keys; Bright message waiting indicator; Desk or wall mountable

*Two-line only

I Series Trimline Analog

- Single or Two line configuration
- Optional message waiting indicator; Flash, Redial, Mute keys
- ADA-compliant volume control with enhanced Sonica™ hearing aid compatibility
- Analog data port

*Two-line only

I SERIES VoIP

SPECIFICATIONS

Standard Color:	Ash and Black
Footprint (Desk):	6.0" (15.24cm) (w) x 9.0" (22.86cm) (l) x 2.125" (5.40cm) (d) (without handset); 6.0" (15.24cm) (w) x 9.0" (22.86cm) (l) x 3.375" (8.57cm) (d) (with handset)
Footprint (Wall):	6.0" (15.24cm) (w) x 9.0" (22.86cm) (l) x 2.0" (5.08cm) (d) (without handset); 6.0" (15.24cm) (w) x 9.0" (22.86cm) (l) x 3.5" (8.89cm) (d) (with handset)
Footprint (RediDock, Cordless) (Desk, Wall):	2.75" (6.99cm) (w) x 8.25" (20.96cm) (l) x 2.25" (5.72cm) (d) (without handset); 2.75" (6.99cm) (w) x 8.25" (20.96cm) (l) x 3.38" (8.59cm) (d) (with handset)
Weight:	1.8 lbs. (0.81kg)
Weight (Redidock, Cordless):	7 oz. (0.2kg) (without handset); 0.8 lbs. (0.36kg) (with handset)
Frequency:	1.9 GHz or 1.8 GHz
Power:	Power over Ethernet (PoE)
Standby Time (Cordless):	14 days

Talk Time (Cordless):	4 hours
Humidity:	65% ± 20%
Temperature:	77°F ± 50° (25°C ± 10°C)
Packaging:	10 per carton
Packaging (RediDock, Cordless):	20 per carton
Faceplate Size:	Full length
FCC Specifications:	Meets or exceeds Part 15, Subpart J, Class A, Part 68
Safety Standard:	ETL and CE
Operating Voltage:	24 to 56 VDC Non-Polarity
Flash Timing:	600 ms
Ringer Equivalence:	Z (Use only behind PBX)
Registered Connector (Corded):	USOC RJ-14
Handset:	Hearing Aid compatible
Line Cord (Cordless):	12-foot, 2 RJ45
Cords & Line (Corded):	12-foot RJ45/10-foot coil

PART NUMBERS

SINGLE-LINE VoIP 1.9 GHz CORDLESS

NDC2105s (5-button speaker)	IV21319S5D3 Ash
	IV11319S5D3 Black

NDC2110s (10-button speaker)	IV21319S10D3 Ash
	IV11319S10D3 Black

RediDock 1.9 GHz (Single-line)	
IRD9110-POE	IV21319N0HK3 Ash
	IV11319N0HK3 Black

TWO-LINE VoIP 1.9 GHz CORDLESS

NDC2205s (5-button speaker)	IV22319S5D3 Ash
	IV12319S5D3 Black

NDC2210s (10-button speaker)	IV22319S10D3 Ash
	IV12319S10D3 Black

RediDock 1.9 GHz (Two-line)	
IRD9210-POE	IV22319N0HK3 Ash
	IV12319N0HK3 Black

SINGLE-LINE VoIP 1.8 GHz CORDLESS

NDC2105S (5-button speaker)	IV21318S5D3 Ash
	IV11318S5D3 Black

NDC2110S (10-button speaker)	IV21318S10D3 Ash
	IV11318S10D3 Black

RediDock 1.8 GHz (Single-line)

IRD8110-POE	IV21318N0HK3 Ash
	IV11318N0HK3 Black

TWO-LINE VoIP 1.8 GHz CORDLESS

NDC2205S (5-button speaker)	IV22318S5D3 Ash
	IV12318S5D3 Black

NDC2210S (10-button speaker)	IV22318S10D3 Ash
	IV12318S10D3 Black

RediDock 1.8 GHz (Two-line)	
IRD8210-POE	IV22318N0HK3 Ash
	IV12318N0HK3 Black

SINGLE-LINE VoIP CORDED

ND2105s (5-button speaker)	IV2105S5D3 Ash
	IV1105S5D3 Black

ND2110s (10-button speaker)	IV2105S10D3 Ash
	IV1105S10D3 Black

TWO-LINE VoIP CORDED

ND2205s (5-button speaker)	IV2205S5D3 Ash
	IV1205S5D3 Black

ND2210s (10-button speaker)	IV2205S10D3 Ash
	IV1205S10D3 Black



I SERIES TRIMLINE ANALOG

SPECIFICATIONS

Standard Color: Ash and Black
Footprint: 2.75" (w) x 8.25" (l) x 3.38" (d) [6.99cm x 20.96cm x 8.59cm]
Weight: 0.8 lbs. (0.36kg)
Power: Line
Humidity: 65% ± 20%
Temperature: 77°F ± 50° [25°C ± 10°C]
Packaging: 20 per carton

FCC Specifications: Meets or exceeds Part 15, Subpart J, Class A, Part 68
Safety Standard: ETL and CE
Operating Voltage: 24 to 56 VDC Non-Polarity
Ringer Equivalence: Z (Use only behind PBX)
Registered Connector: USOC RJ-14
Handset: Hearing Aid compatible
Cords & Line: 10-foot coil/8 -inch line cord

PART NUMBERS

I Series Trimline (Single-line)

AT1101 NO/MW	AT1102 W/MW
IPN33019 Ash	IPN33119 Ash
IPN330191 Black	IPN331191 Black

I Series Trimline 2 (Two-line)

AT1201 NO/MW	AT1202 W/MW
IPN34059 Ash	IPN34159 Ash
IPN340591 Black	IPN341591 Black

I SERIES ANALOG

SPECIFICATIONS

Standard Color: Ash and Black
Footprint (Desk): 6.0" (15.24cm) (w) x 9.0" (22.86cm) (l) x 2.125" (5.40cm) (d) (without handset);
..... 6.0" (15.24cm) (w) x 9.0" (22.86cm) (l) x 3.375" (8.57cm) (d) (with handset)
Footprint (Wall): 6.0" (15.24cm) (w) x 9.0" (22.86cm) (l) x 2.0" (5.08cm) (d) (without handset);
..... 6.0" (15.24cm) (w) x 9.0" (22.86cm) (l) x 3.5" (8.89cm) (d) (with handset)
Footprint (RediDock, Cordless) (Desk, Wall): 2.75" (6.99cm) (w) x 8.25" (20.96cm) (l) x 2.25" (5.72cm) (d) (without handset);
..... 2.75" (6.99cm) (w) x 8.25" (20.96cm) (l) x 3.38" (8.59cm) (d) (with handset)
Weight: 1.8 lbs. (0.81kg)
Weight (Redidock, Cordless): 7 oz. (0.2kg) (without handset)
..... 0.8 lbs. (0.38kg) (with handset)
Frequency (Cordless): 1.9 GHz or 1.8 GHz
Power: Line
(Cordless) 12 VDC adapter

Standby Time (Cordless): 14 days
Talk Time (Cordless): 6 hours
Humidity: 65% ± 20%
Temperature: 77°F ± 50° [25°C ± 10°C]
Packaging: 10 per carton
Packaging (RediDock): 20 per carton
Faceplate Size: Full length
FCC Specifications: Meets or exceeds Part 15, Subpart J, Class A, Part 68
Safety Standard: ETL and CE
Operating Voltage: 24 to 56 VDC Non-Polarity
Flash Timing: 100 ms to 1000 ms
Ringer Equivalence: Z (Use only behind PBX)
Registered Connector (Corded): USOC RJ-14
Handset: Hearing Aid compatible
Line Cord (Cordless): 12-foot, 1-RJ45 and 1-RJ14
Cords & Line (Corded): 12-foot/10-foot coil

PART NUMBERS

SINGLE-LINE ANALOG 1.9 GHz

CORDESS

AC9105s (5-button speaker)
IPN96459 Ash
IPN964591 Black
AC9110s (10-button speaker)
IPN96559 Ash
IPN965591 Black
RediDock 1.9 GHz (Single-line)
IRD9110 Intl.
IPN96559HDKIT Ash
IPN965591HDKIT Black

SINGLE-LINE ANALOG 1.8 GHz

CORDESS

AC8105s Intl. (5-button speaker)
IPN96259 Ash
IPN962591 Black
AC8110s Intl. (10-button speaker)
IPN96359 Ash
IPN963591 Black
RediDock 1.8 GHz (Single-line)
IRD8110 Intl.
IPN96359HDKIT Ash
IPN963591HDKIT Black

TWO-LINE ANALOG 1.9 GHz CORDLESS

AC9205s (5-button speaker)
IPN98459 Ash
IPN984591 Black
AC9210s (10-button speaker)
IPN98559 Ash
IPN985591 Black
RediDock 1.9 GHz (Two-line)
IRD9210 Intl.
IPN98559HDKIT Ash
IPN985591HDKIT Black

TWO-LINE ANALOG 1.8 GHz CORDLESS

AC8205s Intl. (5-button speaker)
IPN98259 Ash
IPN982591 Black
AC8210s Intl. (10-button speaker)
IPN98359 Ash
IPN983591 Black
RediDock 1.8 GHz (Single-line)
IRD8210 Intl.
IPN98359HDKIT Ash
IPN983591HDKIT Black

SINGLE-LINE ANALOG CORDED

A101 (Lobby)

IPN33009 Ash
IPN330091 Black
A100 (Basic)
IPN33309 Ash
IPN333091 Black
A102 (Basic)
IPN33039 Ash
IPN330391 Black
A103 (3-button)
IPN33739 Ash
IPN337391 Black
A105 (5-button)
IPN33139 Ash
IPN331391 Black
A110 (10-button)
IPN33239 Ash
IPN332391 Black
A100s (Basic speaker)
IPN33049 Ash
IPN330491 Black
A103s (3-button speaker)
IPN33749 Ash
IPN337491 Black

A105s (5-button speaker)

IPN33149 Ash
IPN331491 Black
A110s (10-button speaker)
IPN33339 Ash
IPN333391 Black

TWO-LINE ANALOG CORDED

A200s (Basic speaker)

IPN34049 Ash
IPN340491 Black
A203s (3-button speaker)
IPN34749 Ash
IPN347491 Black
A205s (5-button speaker)
IPN34149 Ash
IPN341491 Black
A210s (10-button speaker)
IPN34359 Ash
IPN343591 Black



U.S. Toll Free 1 800 794 8353
Telephone +1 719 638 8821
Fax +1 719 638 8815

info@teledex.com
teledex.com

© 2018 Cetus, Inc. Product specifications and descriptions in this document subject to change without notice.
Cetus®, Teledex®, TeleMatrix®, and Scitec® are trademarks or registered trademarks of Cetus, Inc.

TDX-HS-062018