



**Part Number:** FD4D024R9

Indoor/Outdoor Riser OM4 Distribution Tight Buffer 24f

**Product Description**

FX Indoor/Outdoor OM4 Distribution Tight Buffer 24 Fibers OFNR Non-Unitized Black Jacket

**Technical Specifications**

**Product Overview**

Part Number:	FD4D024R9
Construction Type:	Distribution
Environmental Space:	Indoor/Outdoor
Suitable Applications:	Indoor / Outdoor

**Construction**

**Fiber Cable Construction**

Fiber Type	Fiber Count
OM4	24

Fiber Type:	OM4
Fiber Count:	24
Fiber Color Coding:	Blue, Orange, Green, Brown, Gray, White, Red, Black, Yellow, Violet, Pink, Aqua

**Buffer Specification**

Fiber Type	Buffer Material	Buffer Diameter
OM4	Thermoplastic	900 µm

Cable Core Water Blocking:	Waterblocking Aramid Yarns
----------------------------	----------------------------

**SubUnit Specifications**

Fibers Per Subunit:	24
---------------------	----

**Jacket Specifications**

Number of Jackets:	Single Jacket
--------------------	---------------

**Outer Jacket Material**

Material	Nominal Diameter
PVC	0.325 in (8.3 mm)

Outer Jacket Color:	Black
Number of Outer Jacket Ripcords:	1

**Optical Characteristics**

Effective Modal Bandwidth (EMB):	4700 MHz-km / 500 MHz-km
Fiber Core Diameter:	50/125µm
Max Attenuation at 1300 nm:	1.2 dB/km
Max Attenuation at 850 nm:	3.0 dB/km
Wavelength:	850 nm / 1300 nm
10 Gigabit Ethernet Performance:	550 m / 300 m
1 Gigabit Ethernet Performance:	- / 550 m

Min Overfilled Launch (OFL) Bandwidth:	3500 MHz-km /550 Mhz-km
--	-------------------------

## Mechanical Characteristics

Min Bend Radius During Installation:	20x Cable OD
Min Bend Radius During Operation:	10x Cable OD
Max Tensile Strength During Installation:	56 N (250 lbf)
Max Tensile Strength During Operation:	28 N (125 lbf)

## Temperature Range

Operating Temp Range:	-40C to +70C
Installation Temp Range:	-20C to +70C
Storage Temp Range:	-40C to +70C

## Standards

UL Rating/Flame Test:	Riser
CEC/C(UL) Specification:	OFNR
Telecommunications Standards:	ANSI/ICEA S-104-696
RoHS:	Yes

## History

### Variants

Item #	Color
FD4D024R9	Black

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.