



Main

Product or component type	Load Center
Range of product	QO
Load center type	Main breaker
Line Rated Current	200 A
Number of spaces	30
Short-circuit current	22 kA
Number of circuits	30
Number of tandem circuit breakers	0
Phase	1 phase

Complementary

AWG gauge	AWG 4...250 kcmil (aluminium/copper)
NEMA degree of protection	NEMA 3R outdoor
Cover type	Surface cover
Device composition	Grounding bar (ordered separately)
Electrical connection	Lugs
Wiring configuration	3-wire
Material	Tin plated copper busbar
Enclosure material	Welded galvanized steel
Surface finish	Baked enamel grey
Box number	6R
Product certifications	UL listed
Height	29.84 in (758 mm)
Width	14.76 in (375 mm)

Environment

Offer Sustainability

Not Green Premium product	Not Green Premium product
Compliant - since 1248 - Schneider Electric declaration of conformity	Compliant - since 1248 - Schneider Electric declaration of conformity
Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold
Need no specific recycling operations	Need no specific recycling operations
WARNING: This product can expose you to chemicals including:	WARNING: This product can expose you to chemicals including:
Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
For more information go to www.p65warnings.ca.gov	For more information go to www.p65warnings.ca.gov

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.