



### Main

Product or component type	Miniature circuit-breaker
Range of product	QO
Line Rated Current	20 A 30 A
System Voltage	120/240 V AC
Mounting mode	Plug-in
Poles description	2P
Circuit breaker type	Quad tandem
Circuit breaker application	HACR rated
Electrical connection	Box lugs

### Complementary

Breaking capacity	10 kA at: 120/240 V AC 50/60 Hz
Number of spaces required	2
AWG gauge	AWG 14...AWG 8 (copper or aluminium)
Height	3.22 in
Depth	2.91 in
Width	1.5 in

### Environment

product certifications	CSA UL listed
ambient air temperature for operation	104 °F (40 °C)

### Offer Sustainability

Green Premium product	Green Premium product
Compliant - since 1323 - Schneider Electric declaration of conformity	Compliant - since 1323 - Schneider Electric declaration of conformity
Reference contains SVHC above the threshold - go to CaP for more details	Reference contains SVHC above the threshold
Available	Available
Need no specific recycling operations	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------