



Main

Product or component type	Miniature circuit-breaker
Range of product	QO
Line Rated Current	15 A
System Voltage	240 V AC
Mounting mode	Plug-in
Poles description	3P
Circuit breaker type	High intensity discharge
Circuit breaker application	Not rated
Electrical connection	Pressure plate

Complementary

Breaking capacity	10 kA at: 240 V AC 50/60 Hz
Number of spaces required	3
AWG gauge	AWG 14...AWG 8 (copper or aluminium)
Height	3 in
Depth	2.91 in
Width	2.25 in

Environment

product certifications	CSA UL listed
ambient air temperature for operation	104 °F (40 °C)

Offer Sustainability

Green Premium product	Green Premium product
Compliant - since 1323 - Schneider Electric declaration of conformity	Compliant - since 1323 - Schneider Electric declaration of conformity
Reference contains SVHC above the threshold - go to CaP for more details	Reference contains SVHC above the threshold
Available	Available
Need no specific recycling operations	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------