



Part Number: 7934A

DataTuff® 5e, 4 Bonded-Pr #24 Sol BC, PO Ins, PE Jkt, OSP BURIAL

[Request Sample](#)

Product Description

Industrial Ethernet Cat 5e, 4 Bonded-Pair 24AWG (Solid) Bare Copper, PO Insulation, PE Outer Jacket, OSP BURIAL

Technical Specifications

Product Overview

Suitable Applications:	Industrial Ethernet Cable, Harsh Environments, 200MHz Category 5e, Gigabit Ethernet, 100Base TX, 100BaseVG ANYLAN, 155A TM, 622A TM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, RJ-45 Compatible, Burial, Halogen Free
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
24	Solid	BC - Bare Copper	0.02 in	4

Conductor Count:	8
Total Number of Pairs:	2
Conductor Size:	24 AWG

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PO - Polyolefin	0.038 in	0.009 in

Bonded-Pair:	Yes
--------------	-----

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
LLDPE - Linear Low Density Polyethylene	0.23 in	0.02 in	No

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
9.38 Ohm/1000ft	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
150 pF/ft	15 pF/ft

Delay

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
538 ns/100m	45 ns/100m	70 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. SRL (Structural Return Loss)	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2 dB/100m	65.3 dB	62.3 dB	63 dB	60 dB	63.8 dB	60.8 dB	20 dB	23 dB	100 ± 15 Ohm	102.5 ± 7.5 Ohm
4 MHz	4.1 dB/100m	56.3 dB	53.3 dB	51 dB	49 dB	51.7 dB	48.7 dB	23.6 dB	23 dB	100 ± 15 Ohm	102.5 ± 7.5
8 MHz	5.8 dB/100m	51.8 dB	48.8 dB	46 dB	43 dB	45.7 dB	42.7 dB	25.4 dB	24.5 dB	100 ± 15 Ohm	101 ± 6
10 MHz	6.5 dB/100m	50.3 dB	47.3 dB	43 dB	41 dB	43.8 dB	40.8 dB	26 dB	25 dB	100 ± 15 Ohm	101 ± 6
16 MHz	8.2 dB/100m	47.3 dB	44.3 dB	39 dB	36 dB	39.7 dB	36.7 dB	26 dB	25 dB	100 ± 15 Ohm	101 ± 6
20 MHz	9.3 dB/100m	45.8 dB	42.8 dB	36.5 dB	33.5 dB	37.7 dB	34.7 dB	26 dB	25 dB	100 ± 15 Ohm	101 ± 6
25 MHz	10.4 dB/100m	44.3 dB	41.3 dB	33.9 dB	30.9 dB	35.8 dB	32.8 dB	25.5 dB	24.3 dB	100 ± 15 Ohm	101 ± 6
31.25 MHz	11.7 dB/100m	42.9 dB	39.9 dB	31 dB	28 dB	33.9 dB	30.9 dB	25 dB	23.6 dB	100 ± 15 Ohm	101 ± 6
62.5 MHz	17 dB/100m	38.4 dB	35.4 dB	22 dB	19 dB	27.8 dB	24.8 dB	23.5 dB	21.5 dB	100 ± 15 Ohm	101 ± 6
100 MHz	22 dB/100m	35.3 dB	32.3 dB	14 dB	11 dB	23.8 dB	20.8 dB	22.5 dB	20.1 dB	100 ± 15 Ohm	
155 MHz	28.1 dB/100m	32.5 dB	29.5 dB	4.4 dB	1.4 dB	19.9 dB	16.9 dB	15.8 dB		100 ± 25 Ohm	
200 MHz	32 dB/100m	30.8 dB	27.8 dB	4 dB	1 dB	17.7 dB	14.7 dB	15 dB		100 ± 25 Ohm	

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temp Range:	-25°C To +75°C
UL Temp Rating:	60°C
Storage Temp Range:	-40°C To +85°C
Operating Temp Range:	-40°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	30 lbs/1000ft
Max Recommended Pulling Tension:	40 lbs
Min Bend Radius/Minor Axis:	1 in

Standards

ISO/IEC Compliance:	ISO/IEC 11801 Cat 5e
CPR Euroclass:	Eca
Data Category:	Category 5e
Telecommunications Standards:	TIA-568-C.2 Category 5e
Third Party Performance Verification:	UL Verified Cat 5e

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-04
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes - Telcordia, IEC, ICEA
-----------------------	----------------------------

Suitability - Non-Halogenated:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
7934A 0101000	Black	C

Footnote:	C - CRATE REEL PUT-UP.
Patent:	https://www.belden.com/resources/patents

Product Notes

Notes:	U. S. Patents 5606151 and 5734126. EtherNet IP is a trademark of ControlNet International Ltd. under license by DeviceNet Vendor Association, Inc. Operating Temperature subject to length de-rating.
--------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.