



### Main

Product or component type	Industrial Control Transformer
Rated power in VA	250 VA
Primary voltage	208 V
Secondary voltage	120 V
Range of product	T

### Complementary

Phase	1 phase
Rated power in VA	250 VA per UL 250 VA per CSA 250 VA per NOM 160 VA per CE
Primary voltage	208 V : 120 V
Temperature rise	80 °C
Electrical connection	Screw clamp terminals
Height	3.2 in
Width	3.75 in
Depth	5.3 in
Material	Copper winding
Product compatibility	FSC2

### Environment

product certifications	CE UL listed file E61239 CSA file LR37055 guide 184-N-90
NEMA degree of protection	Not rated (open device)
insulation temperature	266 °F (130 °C)

### Offer Sustainability

Green Premium product	Green Premium product
Compliant - since 1227 - Schneider Electric declaration of conformity	Compliant - since 1227 - Schneider Electric declaration of conformity
Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold
Available	Available
Need no specific recycling operations	Need no specific recycling operations
WARNING: This product can expose you to chemicals including:	WARNING: This product can expose you to chemicals including:
Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	10 Years
-----------------	----------