



GE
Lighting

SAFETY & PERFORMANCE

- ☞ cUL_Listed
- ☞ FCC_CS_NCons
- ☞ UL_Cls_P
- ☞ UL_Listed
- ☞ UL_Type1_Out
- ☞ UL_Type_HL
- ☞ NEMA_Pre
- ☞ Pro_comp_res_req

72269 - GE UltraMax® General Series T8 Electronic Multivolt Instant Start Ballast Electronic Multivolt Instant Start Ballast

GE132MAX-G-N (Replaces GE-132-MV-N)

- ☞ High performance electronic ballast for all general fluorescent applications
- ☞ Instant start electronic ballast for long lamp starting cycles and low initial cost
- ☞ Multi-Voltage Technology handles voltage from 120 to 277V
- ☞ Light-weight, Low Profile Housing
- ☞ Parallel lamp operation means system maintenance is easier to manage
- ☞ Anti-striation Control for better light quality, with no striations

Product Photo



CAUTIONS & WARNINGS

Warning

Risk of Electric Shock

Properly ground ballast and fixture.

Turn power off before servicing--see instructions.

SPECIFICATIONS BY LAMP & WATTAGE

Lamp	# of Lamps	Line Volts	System Watts	Nom. Line Current	System Ballast Factor	Ballast Efficacy Factor	Power Factor% (>=)	Crest Factor (<=)	THD% (<=)	Min. Starting Temp (F/ C)
F17T8	1	120	16	0.14	0.92	6	0.99	1.7	9	0
F17T8	1	277	16	0.07	0.92	6	0.84	1.7	11	0
F25T8	1	120	22	0.19	0.93	4	0.99	1.7	7	0
F28T8	1	120	25	0.21	0.88	4	0.99	1.7	6	60
F28T8	1	277	25	0.09	0.88	4	0.95	1.7	9	60
F25T8	1	277	23	0.09	0.93	4	0.94	1.7	9	0
F32T8/WM	1	120	26	0.22	0.88	3	0.99	1.7	6	60
F32T8/WM	1	277	26	0.1	0.88	3	0.96	1.7	8	60
F32T8	1	277	28	0.1	0.87	3	0.96	1.7	8	-22
F32T8	1	120	28	0.23	0.87	3	0.99	1.7	6	-22
F32T8/25W	1	277	24	0.0	0.88	4	0.97	1.5	10	60