



GE
Lighting

43258 - GE LED HID Lamps

LED80/2M250/740

- ☞ Energy-efficient Value LED lamps. Long life.
- ☞ Open or Enclosed Rated
- ☞ CWA ANSI - M58, M138, M153
- ☞ Not suitable for air-tight explosive or hazardous fixtures
- ☞ For additional collateral click the link below: https://products.currentbyge.com/led-lamps-and-modules/led-replacement-for-hid

Product Photo



GENERAL CHARACTERISTICS

Base Description	EX39 Screw
Base Type	Screw-In
Body Color	Clear
Dimmable	No
Primary Application	Replacement for HID
Product Color	Clear
Product Technology	LED
Rated Life (Hours)	50000 h
Dimmable / Non-Dimmable	No
Lamp Count	1
Life in Years	17.1 yr
Replacement Watts	250 W
Requested Structure	Carton
Estimated Energy Cost per Year	25.7

PHOTOMETRIC CHARACTERISTICS

Rated Beam Spread	80 W
Initial Lumens-nominal	11800 lm
Color Rendering Index-CRI	147.5
Color Temperature	4000 K

PRODUCT INFORMATION

Product Code	43258
Description	LED80/2M250/740
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168432580
Standard Package GTIN	10043168432587
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	
Alternative Unit Of Measure	EACH
Standard Package Quantity	
Ean UPC	043168432580
Standard Package GTIN	00043168432580
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Each
UCC	

DIMENSIONS

Bulb Max Overall Length-MOL	8.4 in
-----------------------------	--------

ELECTRICAL CHARACTERISTICS

Drive Current	17.1
Energy Efficiency Class	yr
Nominal Power (Watts)	250 W
Voltage <Nom>	120 V
Rated power (Watts)	80 W